

Refractometer PAL-2



Since the measurement range of PAL-2 is Brix 45.0 - 93.0%, it can measure various high concentration samples such as jam, marmalade, jelly, honey and concentrated juice. The International Protection class of PAL-2 is IP65, so it can clean thick samples under running water. If you measure boiling jam or marmalade, we recommend [PAL-H](#)

Specifications

Model	PAL-2
Cat.No.	3820
Range	Brix : 45.0 to 93.0 %
Resolution	Brix : 0.1%
Accuracy	±0.2 %



Shop



Quotation Request



Send an inquiry

Accessories

- STRAP : RE-39410
- PAL-CASE : RE-39409
- JORDAN for PAL(Silicon Cover) : RE-39414
- 50% Sucrose (±0.05%) : RE-110050
- 60% Sucrose (±0.05%) : RE-110060
- Battery Case Cover With O-Ring : RE-38163
- AC Battery Charger : RE-34802
- * Calibration Certificate : Contact an ATAGO representative for details.