

Refractometer PAL-S



Shop



Quotation Request



Send an inquiry

Improved Repeatability with Mode STM Technology.

Mode STM is the solution to fluctuating measurement values. Ideal for fatty and/or dark samples, such as dairy products.

Specifications

Model	PAL-S
Cat.No.	3860
Range	Brix : 0.0 to 93.0 %
Resolution	Brix : 0.1% Temperature : 0.1°C
Accuracy	±0.2 %

Accessories

- PAL-CASE : RE-39409
- JORDAN for PAL(Silicon Cover) : RE-39414
- SUPER EXTRACTOR : RE-29401
- STRAP : RE-39410
- 10% Sucrose (±0.03%) : RE-110010
- 20% Sucrose (±0.03%) : RE-110020
- 30% Sucrose (±0.03%) : RE-110030
- 40% Sucrose (±0.04%) : RE-110040
- 50% Sucrose (±0.05%) : RE-110050
- 60% Sucrose (±0.05%) : RE-110060
- Battery Case Cover With O-Ring : RE-38163
- AC Battery Charger : RE-34802
- * Calibration Certificate : Contact an ATAGO representative for details.
- MAGIC TM (for PAL MIM) : RE-39446