12/26/22, 12:05 PM PEN-PRO



CLOSE

Digital Hand-held PEN-PRO







Shop



Quotation Request



Send an inquiry

The PEN-PRO has a measurement range of Brix 0.0 to 85.0% which can be used to measure almost any sample. There are 2 ways to measure with the PEN-PRO. Either dip the tip into the sample and press the START key OR press the START key and touch the tip into the sample. There is also the new feature to perform continuous measurements. The temperature range of the "Dip-Type" Refractometer PEN-PRO has been improved from 60°C to 100°C. No more wait! Measure hot samples while in the cooking process, such as soups and sauces.

Specifications

| ^ | |
|--------------------------|-------------------------------|
| Model | PEN-PRO |
| Cat.No. | 3730 |
| Range | Brix: 0.0 to 85.0% |
| Accuracy | ± 0.2% |
| Temperature compensation | 10 to 100°C |
| Measurement Time | 2 seconds |
| Power Supply | 1 × Size AAA alkaline battery |

Accessories

· AC Battery Charger: RE-34802

· STRAP: RE-39410

* Calibration Certificate: Contact an ATAGO representative for details.

(C) 2003-2022 ATAGO CO.,LTD, All rights reserved. CLOSE

