



**MS 3 basic** /// Data Sheet

Compact, universal small shaker suitable for shaking tasks with all small vessels and microtiter plates

- Wide range of attachments
- Attachment detection
- Continuous or touch operation (with standard attachment)
- Two operating modes:
- Mode A (safe mode with attachment detection)

the maximum speed of 3.000 rpm is only reached with the standard attachment in

www.ika.com Subject to technical changes



touch mode. When using other attachments the speed is limited to 1.300 rpm.

Mode B (without attachment detection)

a speed of 3000 rpm is possible with all attachments, depending on the application (see the speed range of the accessory list)

- Stable in all speed ranges

- Sturdy zinc die cast casing



## **Technical Data**

Type of movement	orbital	
Shaking stroke [mm]	4.5	
Permissible shaking weight (incl. attachment) [kg]	0.5	
Motor rating input [W]	10	
Motor rating output [W]	8	
Permissible ON time [%]	100	
Speed min (adjustable) [rpm]	200	
Speed range [rpm]	0 - 3000	
Speed display	scale	
Operating mode	continuous operation	
Touch function	yes	
Working with microtiter plates	yes	
Number of microtiter plates	1	
Dimensions (W x H x D) [mm]	148 x 63 x 205	
Weight [kg]	2.9	
Permissible ambient temperature [°C]	5 - 40	
Permissible relative humidity [%]	80	
Protection class according to DIN EN 60529	IP 21	
Voltage [V]	100 - 240	
Frequency [Hz]	50/60	
Power input [W]	20	
DC Voltage [V=]	24	
Current consumption [mA]	800	