



# FP4

## Flocculator

Portable Jar Tester with 4 position, timer and lighting system



# Practical and reliable solution for on-site Jar Test

Portable flocculator in 4 positions that allows standard conditions to be adopted for jar test.

- Choice of 20-40-50-100-200 rpm stirring speeds
- Precise speed from an electronically controlled DC gear motor
- 4 samples can be processed in parallel
- Designed to be used on-site for immediate results
- Strong resistance to chemical and mechanical corrosion
- Central light to facilitate reading



## INSTRUMENT - CODE

FP4

100-240 V / 50-60 Hz

F105A0117

## TECHNICAL DATA

	FP4
CONSTRUCTION MATERIAL	Epoxy painted metal structure
NUMBER OF SAMPLES	4 positions
STAINLESS STEEL STIRRING RODS	Adjustable in height by a selflocking chuck
MONOSELECTOR	Same speed for each rod
ELECTRONIC SPEED CONTROL	20 - 40 - 50 - 100 - 200 rpm
TIMER	from 0 to 30 minutes (or continuous)
POWER	6 W
DIMENSIONS (WXHXD)	250x320x250 mm (9.8x12.6x9.8 in)
WEIGHT	4,8 Kg (10.6 lb)



We reserve the right to make technical alterations  
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

## DESIGNED AND MANUFACTURED IN ITALY



**ITALY - HQ**  
Via Stazione 16  
20865 Usmate (MB) Italy  
Tel. +39 039 628811  
velpitalia@velp.com

**INDIA**  
velpindia@velp.com

**USA**  
155 Keyland Court, Bohemia  
NY 11716 - U.S.  
Tel. +1 631 573 6002  
velpusa@velp.com

**CHINA**  
Xinlong Rd Building 28, Lane 1333  
Shanghai city - China  
Tel. +86 18017557329  
velpchina@velp.com